

Quick-Change Mounting Plate

with zero point clamping system SPEEDY easy click for modulog interfaces



Advantages

- modulog interface
- Workpiece change in seconds by SPEEDY easy click
- Engages immediately without any energy supply!
- Immediate build up of the clamping force 5 kN
- Max. retention force 10 kN
- Pneumatics for unclamping available everywhere
- Radial positioning by locating bolts
- Snapper as a safety against falling out in the changing position

Description

The quick-change mounting plate is designed as adaptor plate with connecting dimensions of the modulog interface 140 x 140.

A STARK zero point clamping system SPEEDY easy click is installed in the centre.

This is a fast-closing clamp plate that engages immediately and clamps without energy supply. For unclamping a pneumatic connection is required.

The required draw-in nipple is mounted on the base plate for the workpiece to be clamped. The radial positioning is made by a location bolt. A suitable drill bush is embedded in the base plate. In addition, there is a snapper installed to secure the workpiece against falling out after the pneumatic unclamping of the zero point clamping element.

modulog

Quick-change mounting plate for SPEEDY easy click

Lifting module Shop Floor

as per data sheet M 4.301



Part no. 890301P

Combinable with the modules

- Rotating module with flow power as per data sheet M 1.202

modulog interface

• 140 x 140 - M10


Technical data

loonnour autu		
Clamping force (traction) approx.	[kN]	5
Retention force maxi.	[kN]	10
Force to engage approx.	[N]	80
Pneumatic unclamping pressure	[bar]	3–8
Clamping time approx.	[S]	0.1
Unclamping time approx.	[S]	0.1
Admissible workpiece weight	[kg]	100
Admissible side load	[kN]	2.5
Admissible radial torque	[Nm]	200
Repeatability	[mm]	0.01
Weight, approx.	[kg]	8.2
Accessories		
Draw-in nipple (1 piece)	6200-776	

Workpiece change



Workpiece engaged



Application

The quick-change mounting plate can be mounted onto all modulog modules and devices with interface 140 x 140 mm.

The built-in STARK zero point clamping system SPEEDY easy click allows a very fast workpiece change.


A prerequisite is that the workpieces are mounted on base plates which are equipped with a draw-in nipple for the SPEEDY easy click.

This system is particularly suitable,

- when workpieces must be frequently changed very quickly at the assembly station.
- when different workpieces or parts families are to be routed through one assembly station.
- when workpieces are to be routed through several assembly stations.
- when the workpiece with the required base plate is still manually tradable.

□170 ±0,2 □140 ±0,1

70 ±0.1



Quick-changing mounting plate with SPEEDY easy click